

Garant GRIDLINE

Base cabinet with plain sheet metal swing doors, Height: 750mm**Order data**

Order number	940841 750
GTIN	4062406070656
Item class	9GI

Description**Version:**

Empty cabinet in 40×20G. Suitable drawers: 36×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	595 mm
Width in G	40
Weight	41 kg
ComfortClose	no
Height	750 mm

Width	1000 mm
Handle positioning	top
Type of cabinet	Base cabinet
Depth	500 mm
Cabinet fronts	Plain sheet metal swing door
Depth in G	20
Electronic locking system can be retrofitted	yes
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Drawer for swing-door cabinets,Width 40G Drawer front height 300 mm	940642 300
Extended lighting set for GridLine cabinets withSwing doors, width 40G for cabinet height 750/800 mm	940511 750/800
Storage shelf for cabinet / compartment width in G 40	940550 40
Drawer for swing-door cabinets,Width 40G Drawer front height 150 mm	940642 150
Drawer for swing-door cabinets,Width 40G Drawer front height 125 mm	940642 125
Storage shelf200 kg for cabinet / compartment width in G 40	940590 40
	940552 40

Storage shelf slotted for cabinet / compartment width in G 40

Drawer for swing-door cabinets,Width 40G Drawer front height 100 mm

940642 100

Inclined shelf for cabinet / compartment width in G 40

940560 40

Slide handle for GridLine Type GP11

914226 GP11

Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm

940501 750/800

Drawer for swing-door cabinets,Width 40G Drawer front height 200 mm

940642 200

Drawer for swing-door cabinets,Width 40G Drawer front height 75 mm

940642 75