

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 2000mm**Order data**

Order number	940843 2000
GTIN	4062406070786
Item class	9GI

Description**Version:**

Empty cabinet in 40×20G. Suitable drawers: 36×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	20
Electronic locking system can be retrofitted	yes
Height	2000 mm
Usable height	1845 mm

Weight	81 kg
ComfortClose	no
Depth	500 mm
Width in G	40
Handle positioning	centre
Cabinet fronts	Viewing window swing door
Width	1000 mm
Type of cabinet	Base cabinet
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Drawer for swing-door cabinets,Width 40G Drawer front height 200 mm	940642 200
Drawer for swing-door cabinets,Width 40G Drawer front height 150 mm	940642 150
Drawer for swing-door cabinets,Width 40G Drawer front height 300 mm	940642 300
Extended lighting set for GridLine cabinets withSwing doors, width 40G for cabinet height 2000 mm	940511 2000
Drawer for swing-door cabinets,Width 40G Drawer front height 100 mm	940642 100
	940642 75

Drawer for swing-door cabinets,Width 40G Drawer front height 75 mm

Storage shelf for cabinet / compartment width in G 40

940550 40

Storage shelf slotted for cabinet / compartment width in G 40

940552 40

Inclined shelf for cabinet / compartment width in G 40

940560 40

Storage shelf200 kg for cabinet / compartment width in G 40

940590 40

Slide handle for GridLine Type GP11

914226 GP11

Drawer for swing-door cabinets,Width 40G Drawer front height 125 mm

940642 125

Basic lighting set for GridLine cabinets withswing doors for cabinet height 2000 mm

940501 2000