

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 1500mm



Order data

Order number	940843 1500
GTIN	4062406070779
Item class	9GI

Description

Version:

Empty cabinet in 40×20G. Suitable drawers: 36×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	20
Depth	500 mm
Cabinet fronts	Viewing window swing door
Handle positioning	top

ComfortClose	no
Width in G	40
Type of cabinet	Base cabinet
Height	1500 mm
Width	1000 mm
Weight	65 kg
Usable height	1345 mm
Electronic locking system can be retrofitted	yes
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Basic lighting set for GridLine cabinets with swing doors for cabinet height 1500 mm	940501 1500
Drawer for swing-door cabinets, Width 40G Drawer front height 75 mm	940642 75
Drawer for swing-door cabinets, Width 40G Drawer front height 300 mm	940642 300
Drawer for swing-door cabinets, Width 40G Drawer front height 150 mm	940642 150
Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40
	940511 1500

Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 1500 mm

Drawer for swing-door cabinets, Width 40G Drawer front height 200 mm

940642 200

Drawer for swing-door cabinets, Width 40G Drawer front height 100 mm

940642 100

Drawer for swing-door cabinets, Width 40G Drawer front height 125 mm

940642 125

Storage shelf slotted for cabinet / compartment width in G 40

940552 40

Slide handle for GridLine Type GP11

914226 GP11

Inclined shelf for cabinet / compartment width in G 40

940560 40

Storage shelf for cabinet / compartment width in G 40

940550 40