

Garant GRIDLINE

**Base cabinet with plain sheet metal swing doors, Height: 1500mm****Order data**

Order number	940841 1500
GTIN	4062406070700
Item class	9GI

**Description****Version:**

Empty cabinet in 40×20G. Suitable drawers: 36×16G (please order these separately)  
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Depth in G	20
ComfortClose	no
Usable height	1345 mm
Height	1500 mm

Cabinet fronts	Plain sheet metal swing door
Depth	500 mm
Width in G	40
Type of cabinet	Base cabinet
Electronic locking system can be retrofitted	yes
Width	1000 mm
Handle positioning	top
Weight	65 kg
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

## Accessories

Drawer for swing-door cabinets,Width 40G Drawer front height 75 mm	940642 75
Slide handle for GridLine Type GP11	914226 GP11
Storage shelf200 kg for cabinet / compartment width in G 40	940590 40
Storage shelf for cabinet / compartment width in G 40	940550 40
Drawer for swing-door cabinets,Width 40G Drawer front height 300 mm	940642 300
Drawer for swing-door cabinets,Width 40G Drawer front height 100 mm	940642 100

Inclined shelf for cabinet / compartment width in G 40	940560 40
Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 1500 mm	940511 1500
Drawer for swing-door cabinets, Width 40G Drawer front height 200 mm	940642 200
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Drawer for swing-door cabinets, Width 40G Drawer front height 125 mm	940642 125
Drawer for swing-door cabinets, Width 40G Drawer front height 150 mm	940642 150
Basic lighting set for GridLine cabinets with swing doors for cabinet height 1500 mm	940501 1500