

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 750mm



Order data

Order number	940843 750
GTIN	4062406070724
Item class	9GI

Description

Version:

Empty cabinet in 40×20G. Suitable drawers: 36×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	750 mm
ComfortClose	no
Width	1000 mm
Electronic locking system can be retrofitted	yes
Type of cabinet	Base cabinet

Width in G	40
Handle positioning	top
Depth in G	20
Cabinet fronts	Viewing window swing door
Usable height	595 mm
Depth	500 mm
Weight	41 kg
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Drawer for swing-door cabinets,Width 40G Drawer front height 200 mm	940642 200
Inclined shelf for cabinet / compartment width in G 40	940560 40
Drawer for swing-door cabinets,Width 40G Drawer front height 75 mm	940642 75
Drawer for swing-door cabinets,Width 40G Drawer front height 150 mm	940642 150
Drawer for swing-door cabinets,Width 40G Drawer front height 100 mm	940642 100
Drawer for swing-door cabinets,Width 40G Drawer front height 125 mm	940642 125
	940511 750/800

Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 750/800 mm

Storage shelf for cabinet / compartment width in G 40

940550 40

Storage shelf 200 kg for cabinet / compartment width in G 40

940590 40

Basic lighting set for GridLine cabinets with swing doors for cabinet height 750/800 mm

940501 750/800

Drawer for swing-door cabinets, Width 40G Drawer front height 300 mm

940642 300

Storage shelf slotted for cabinet / compartment width in G 40

940552 40

Slide handle for GridLine Type GP11

914226 GP11