

Garant GRIDLINE

Base cabinet with plain sheet metal swing doors, Height: 1000mm**Order data**

Order number	940841 1000
GTIN	4062406070687
Item class	9GI

Description**Version:**

Empty cabinet in 40×20G. Suitable drawers: 36×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	845 mm
Depth in G	20
Type of cabinet	Base cabinet
Height	1000 mm

ComfortClose	no
Weight	49 kg
Electronic locking system can be retrofitted	yes
Depth	500 mm
Cabinet fronts	Plain sheet metal swing door
Handle positioning	top
Width in G	40
Width	1000 mm
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40
Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 1000/1250 mm	940511 1000/1250
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets, Width 40G Drawer front height 200 mm	940642 200
Drawer for swing-door cabinets, Width 40G Drawer front height 100 mm	940642 100

Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm	940501 900/1000
Drawer for swing-door cabinets, Width 40G Drawer front height 150 mm	940642 150
Drawer for swing-door cabinets, Width 40G Drawer front height 300 mm	940642 300
Storage shelf for cabinet / compartment width in G 40	940550 40
Drawer for swing-door cabinets, Width 40G Drawer front height 125 mm	940642 125
Inclined shelf for cabinet / compartment width in G 40	940560 40
Drawer for swing-door cabinets, Width 40G Drawer front height 75 mm	940642 75