

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 1250mm



Order data

Order number	940843 1250
GTIN	4062406070762
Item class	9GI

Description

Version:

Empty cabinet in 40×20G. Suitable drawers: 36×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
Handle positioning	top
Width in G	40
Weight	57 kg

Depth in G	20
Usable height	1095 mm
Type of cabinet	Base cabinet
Depth	500 mm
Cabinet fronts	Viewing window swing door
ComfortClose	no
Height	1250 mm
Width	1000 mm
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Basic lighting set for GridLine cabinets with swing doors for cabinet height 1250 mm	940501 1250
Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40
Drawer for swing-door cabinets, Width 40G Drawer front height 75 mm	940642 75
Drawer for swing-door cabinets, Width 40G Drawer front height 200 mm	940642 200
	940642 150

Drawer for swing-door cabinets,Width 40G Drawer front height 150 mm

Slide handle for GridLine Type GP11

914226 GP11

Drawer for swing-door cabinets,Width 40G Drawer front height 100 mm

940642 100

Drawer for swing-door cabinets,Width 40G Drawer front height 125 mm

940642 125

Inclined shelf for cabinet / compartment width in G 40

940560 40

Storage shelf for cabinet / compartment width in G 40

940550 40

Extended lighting set for GridLine cabinets withSwing doors, width 40G for cabinet height 1000/1250 mm

940511 1000/1250

Drawer for swing-door cabinets,Width 40G Drawer front height 300 mm

940642 300