



## Swing door cabinet with plain sheet metal swing doors, Height: 2000mm



### Order data

Order number	949501 2000
GTIN	4062406081928
Item class	92S

### Description

#### Version:

Body and doors made of sheet metal, storage shelf mountings at 40 mm intervals. Doors reinforced on the inside and can be locked by push handle with a **cylinder lock**. For more information on locking see No. 950050 – 950060.

With plain sheet metal swing doors.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Cabinet fronts	Plain sheet metal swing door
Height	2000 mm
Usable height	1840 mm
Depth	400 mm

Electronic locking system can be retrofitted	yes
Width	1000 mm
Weight	69 kg
Handle positioning	centre
Number of shelves	4
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	60 kg
Cabinet housing internal load capacity	500 kg
Door opening angle	225 degrees
Height adjustment interval	40 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

---

## Accessories

Additional storage shelf Type 1000	949514 1000
------------------------------------	-------------