



Swing door cabinet with plain sheet metal swing doors, Height: 1200mm



Order data

Order number	949501 1200
GTIN	4062406081911
Item class	92S

Description

Version:

Body and doors made of sheet metal, storage shelf mountings at 40 mm intervals. Doors reinforced on the inside and can be locked by push handle with a **cylinder lock**. For more information on locking see No. 950050 – 950060.

With plain sheet metal swing doors.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
Cabinet fronts	Plain sheet metal swing door
Width	1000 mm
Weight	36 kg

Depth	400 mm
Number of shelves	2
Usable height	1040 mm
Handle positioning	top
Height	1200 mm
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	60 kg
Cabinet housing internal load capacity	500 kg
Door opening angle	225 degrees
Height adjustment interval	40 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

Accessories

Additional storage shelf Type 1000	949514 1000
------------------------------------	-------------