



Swing door cabinet with viewing window swing doors, Height: 1200mm



Order data

Order number	949503 1200
GTIN	4062406080570
Item class	92S

Description

Version:

Body and doors made of sheet metal, storage shelf mountings at 40 mm intervals. Doors reinforced on the inside and can be locked by push handle with a **cylinder lock**. For more information on locking see No. 950050 – 950060.

With viewing window swing doors (polycarbonate windows).

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Cabinet fronts	Viewing window swing door
Width	1000 mm
Number of shelves	2
Usable height	1040 mm

Electronic locking system can be retrofitted	yes
Depth	400 mm
Height	1200 mm
Handle positioning	top
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	60 kg
Cabinet housing internal load capacity	500 kg
Door opening angle	225 degrees
Height adjustment interval	40 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

Accessories

Additional storage shelf Type 1000	949514 1000
------------------------------------	-------------