



Cabinet without doors, Height: 1200mm



Order data

Order number	949506 1200
GTIN	4062406080600
Item class	92S

Description

Version:

Body and doors made of sheet metal, storage shelf mountings at 40 mm intervals. Doors reinforced on the inside and can be locked by push handle with a **cylinder lock**. For more information on locking see No. 950050 – 950060.

Without doors, as open shelf cabinet.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	400 mm
Height	1200 mm
Number of shelves	2
Cabinet fronts	open

Usable height	1040 mm
Width	1000 mm
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	60 kg
Cabinet housing internal load capacity	500 kg
Height adjustment interval	40 mm
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

Accessories

Additional storage shelf Type 1000	949514 1000
------------------------------------	-------------