

**Swing door cabinet with storage shelves, Height mm / Model: 1950/A****Order data**

Order number	949531 1950/A
GTIN	4062406080594
Item class	92S

Description**Version:**

Body and doors made of sheet metal, storage shelf mountings at 40 mm intervals. Doors reinforced on the inside and can be locked by push handle with a **cylinder lock**. Complete with **4 shelves** made of galvanised sheet metal.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	74 kg
Width	950 mm
Number of shelves	4
Usable height	1820 mm

Handle positioning	centre
Depth	430 mm
Height	1950 mm
Cabinet fronts	Plain sheet metal swing door
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	80 kg
Cabinet housing internal load capacity	500 kg
Door opening angle	250 degrees
Height adjustment interval	40 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

Accessories

Additional storage shelf Type 950	949534 950
-----------------------------------	------------