

Garant GRIDLINE

Base cabinet with Plain sheet metal sliding doors, Height: 1500mm**Order data**

Order number	940865 1500
GTIN	4062406071059
Item class	9GI

Description**Version:**

Empty cabinet in 50×20G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width in G	50
Width	1250 mm
Cabinet fronts	Plain sheet metal sliding door
Depth in G	20

Usable height	1345 mm
Depth	500 mm
ComfortClose	no
Weight	104 kg
Electronic locking system can be retrofitted	yes
Type of cabinet	Base cabinet
Height	1500 mm
Handle positioning	top
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Lock plate for GridLine Type GP21	914227 GP21
Storage shelf slotted for cabinet / compartment width in G 50	940552 50
Storage shelf for cabinet / compartment width in G 50	940550 50
Extended lighting set for GridLine cabinets with Sliding doors, width 50G for cabinet height 1500 mm	940513 1500
Storage shelf 200 kg for cabinet / compartment width in G 50	940590 50
Inclined shelf for cabinet / compartment width in G 50	940560 50