

Garant GRIDLINE

Base cabinet with plain sheet metal swing doors, Height: 1250mm



Order data

Order number	940861 1250
GTIN	4062406070908
Item class	9GI

Description

Version:

Empty cabinet in 50×20G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
Depth	500 mm
Weight	91 kg
Cabinet fronts	Plain sheet metal swing door

Handle positioning	top
Depth in G	20
Usable height	1095 mm
Width	1250 mm
ComfortClose	no
Type of cabinet	Base cabinet
Height	1250 mm
Width in G	50
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Basic lighting set for GridLine cabinets with swing doors for cabinet height 1250 mm	940501 1250
Storage shelf 200 kg for cabinet / compartment width in G 50	940590 50
Storage shelf slotted for cabinet / compartment width in G 50	940552 50
Slide handle for GridLine Type GP11	914226 GP11
Storage shelf for cabinet / compartment width in G 50	940550 50
Extended lighting set for GridLine cabinets with Swing doors, width 50G for cabinet height 1000/1250 mm	940512 1000/1250

Inclined shelf for cabinet / compartment width in G 50

940560 50