

Garant GRIDLINE

## Base cabinet with Plain sheet metal sliding doors, Height: 750mm



### Order data

Order number	940865 750
GTIN	4062406071004
Item class	9GI

### Description

#### Version:

Empty cabinet in 50×20G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Type of cabinet	Base cabinet
Weight	65 kg
Cabinet fronts	Plain sheet metal sliding door
Electronic locking system can be retrofitted	yes
Handle positioning	top
Depth in G	20

Usable height	595 mm
Depth	500 mm
Height	750 mm
ComfortClose	no
Width in G	50
Width	1250 mm
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

## Accessories

Inclined shelf for cabinet / compartment width in G 50	940560 50
Storage shelf slotted for cabinet / compartment width in G 50	940552 50
Storage shelf for cabinet / compartment width in G 50	940550 50
Extended lighting set for GridLine cabinets with Sliding doors, width 50G for cabinet height 750/800 mm	940513 750/800
Storage shelf 200 kg for cabinet / compartment width in G 50	940590 50
Lock plate for GridLine Type GP21	914227 GP21