

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 1000mm**Order data**

Order number	940863 1000
GTIN	4062406070960
Item class	9GI

Description**Version:**

Empty cabinet in 50×20G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	1000 mm
Cabinet fronts	Viewing window swing door
Usable height	845 mm
Handle positioning	top
Width in G	50

Width	1250 mm
Depth in G	20
Weight	78 kg
ComfortClose	no
Type of cabinet	Base cabinet
Electronic locking system can be retrofitted	yes
Depth	500 mm
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Extended lighting set for GridLine cabinets with Swing doors, width 50G for cabinet height 1000/1250 mm	940512 1000/1250
Inclined shelf for cabinet / compartment width in G 50	940560 50
Slide handle for GridLine Type GP11	914226 GP11
Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm	940501 900/1000
Storage shelf 200 kg for cabinet / compartment width in G 50	940590 50
Storage shelf slotted for cabinet / compartment width in G 50	940552 50
Storage shelf for cabinet / compartment width in G 50	940550 50