

Garant GRIDLINE

Base cabinet with Plain sheet metal sliding doors, Height: 800mm



Order data

Order number	940885 800
GTIN	4062406071158
Item class	9GI

Description

Version:

Empty cabinet in 60×20G. Suitable drawers: 26×14G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	645 mm
ComfortClose	no
Weight	71 kg
Cabinet fronts	Plain sheet metal sliding door
Depth in G	20
Depth	500 mm
Width	1500 mm

Width in G	60
Height	800 mm
Type of cabinet	Base cabinet
Electronic locking system can be retrofitted	yes
Handle positioning	top
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Storage shelf 200 kg for cabinet / compartment width in G 30	940590 30
Drawer for sliding door cabinets, Width 30G Drawer front height 100 mm	940651 100
Lock plate for GridLine Type GP21	914227 GP21
Drawer for sliding door cabinets, Width 30G Drawer front height 150 mm	940651 150
Drawer for sliding door cabinets, Width 30G Drawer front height 200 mm	940651 200
Inclined shelf for cabinet / compartment width in G 30	940560 30
Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Drawer for sliding door cabinets, Width 30G Drawer front height 300 mm	940651 300
	940651 125

Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm

Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm

940651 75

Storage shelf for cabinet / compartment width in G 30

940550 30

Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 750/800 mm

940514 750/800