

Garant GRIDLINE

## Base cabinet with Viewing window sliding doors, Height: 900mm



### Order data

Order number	940887 900
GTIN	4062406071233
Item class	9GI

### Description

#### Version:

Empty cabinet in 60×20G. Suitable drawers: 26×14G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Type of cabinet	Base cabinet
Depth in G	20
Width in G	60
Weight	75 kg
Handle positioning	top
Width	1500 mm
Electronic locking system can be retrofitted	yes

Usable height	745 mm
Height	900 mm
Cabinet fronts	Viewing window sliding door
ComfortClose	no
Depth	500 mm
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

## Accessories

Drawer for sliding door cabinets,Width 30G Drawer front height 100 mm	940651 100
Inclined shelf for cabinet / compartment width in G 30	940560 30
Drawer for sliding door cabinets,Width 30G Drawer front height 150 mm	940651 150
Storage shelf200 kg for cabinet / compartment width in G 30	940590 30
Lock plate for GridLine Type GP21	914227 GP21
Drawer for sliding door cabinets,Width 30G Drawer front height 200 mm	940651 200
Drawer for sliding door cabinets,Width 30G Drawer front height 300 mm	940651 300
Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 900 mm	940514 900
Storage shelf for cabinet / compartment width in G 30	940550 30

Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm

940651 125

Storage shelf slotted for cabinet / compartment width in G 30

940552 30

Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm

940651 75