


Garant GRIDLINE

## Base cabinet with Viewing window sliding doors, Height: 1000mm



### Order data

Order number	940907 1000
GTIN	4062406071387
Item class	9GI

### Description

#### Version:

Empty cabinet in 80×20G. Suitable drawers: 36×14G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Width	2000 mm
Electronic locking system can be retrofitted	yes
Width in G	80
Depth in G	20
Handle positioning	top
Usable height	845 mm
ComfortClose	no

Cabinet fronts	Viewing window sliding door
Weight	98 kg
Depth	500 mm
Type of cabinet	Base cabinet
Height	1000 mm
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

## Accessories

Lock plate for GridLine Type GP21	914227 GP21
Storage shelf for cabinet / compartment width in G 40	940550 40
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Inclined shelf for cabinet / compartment width in G 40	940560 40
Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40
Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 1000/1250 mm	940515 1000/1250