

Garant GRIDLINE

Base cabinet with Plain sheet metal sliding doors, Height: 2000mm**Order data**

Order number	940905 2000
GTIN	4062406071349
Item class	9GI

Description**Version:**

Empty cabinet in 80×20G. Suitable drawers: 36×14G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	1845 mm
Depth in G	20
ComfortClose	no
Width	2000 mm

Handle positioning	centre
Width in G	80
Height	2000 mm
Cabinet fronts	Plain sheet metal sliding door
Type of cabinet	Base cabinet
Depth	500 mm
Weight	155 kg
Electronic locking system can be retrofitted	yes
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Inclined shelf for cabinet / compartment width in G 40	940560 40
Storage shelf for cabinet / compartment width in G 40	940550 40
Lock plate for GridLine Type GP21	914227 GP21
Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 2000 mm	940515 2000
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40