

Garant GRIDLINE

Base cabinet with Plain sheet metal sliding doors, Height: 900mm**Order data**

Order number	940905 900
GTIN	4062406071301
Item class	9GI

Description**Version:**

Empty cabinet in 80×20G. Suitable drawers: 36×14G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	20
Width in G	80
Width	2000 mm
Handle positioning	top
Weight	92 kg
Depth	500 mm
ComfortClose	no

Type of cabinet	Base cabinet
Usable height	745 mm
Electronic locking system can be retrofitted	yes
Height	900 mm
Cabinet fronts	Plain sheet metal sliding door
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 900 mm	940515 900
Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Lock plate for GridLine Type GP21	914227 GP21
Inclined shelf for cabinet / compartment width in G 40	940560 40
Storage shelf for cabinet / compartment width in G 40	940550 40