

Garant GRIDLINE

Large-capacity base cabinet with plain sheet metal swing doors, Height: 1000mm**Order data**

Order number	941001 1000
GTIN	4062406071424
Item class	9GI

Description**Version:**

Equipped cabinet in 30×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Handle positioning	top
ComfortClose	no
Usable height	845 mm
Width	750 mm
Depth	700 mm
Electronic locking system can be retrofitted	yes
Width in G	30
Weight	70 kg
Height	1000 mm
Depth in G	28
Number of shelves	1
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Large-capacity cabinet

Accessories

Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm	940501 900/1000
Slide handle for GridLine Type GP11	914226 GP11
Inclined shelf foreForm for cabinet / compartment width in G 30	942550 30

Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 300 mm	942570 300
Wheels and push handle retrofit set suitable for casing depth in G 28	958480 28
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 150 mm	942570 150
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 200 mm	942570 200
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 75 mm	942570 75
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 1000/1250 mm	940510 1000/1250
Push handle Type 1	958490 1
Storage shelf with brackets100 kg for cabinet / compartment width in G 30	942530 30
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 100 mm	942570 100
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 125 mm	942570 125