

Garant GRIDLINE

Large-capacity base cabinet with plain sheet metal swing doors, Height: 2000mm**Order data**

| | |
|--------------|---------------|
| Order number | 941001 2000 |
| GTIN | 4062406071431 |
| Item class | 9GI |

Description**Version:**

Equipped cabinet in 30×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|------------|----|
| Width in G | 30 |
|------------|----|

| | |
|---|--|
| Number of shelves | 4 |
| Width | 750 mm |
| Electronic locking system can be retrofitted | yes |
| Depth | 700 mm |
| Weight | 128 kg |
| Shelf load capacity / maximum distributed shelf load (on metal) | 100 kg |
| Depth in G | 28 |
| Usable height | 1845 mm |
| ComfortClose | no |
| Height | 2000 mm |
| Handle positioning | centre |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1000 kg |
| Door opening angle | 250 degrees |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of cabinet | Base cabinet |
| Type of product | Large-capacity cabinet |

Accessories

| | |
|--|------------|
| Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 125 mm | 942570 125 |
| Inclined shelf foreForm for cabinet / compartment width in G 30 | 942550 30 |
| Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 75 mm | 942570 75 |

| | |
|--|-------------|
| Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 200 mm | 942570 200 |
| Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 300 mm | 942570 300 |
| Shelf clip set for GridLine cabinets20 pieces Type F | 940559 F |
| Basic lighting set for GridLine cabinets withswing doors for cabinet height 2000 mm | 940501 2000 |
| Extended lighting set for GridLine cabinets withSwing doors, width 30G for cabinet height 2000 mm | 940510 2000 |
| Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 100 mm | 942570 100 |
| Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 150 mm | 942570 150 |
| Storage shelf with brackets100 kg for cabinet / compartment width in G 30 | 942530 30 |
| Slide handle for GridLine Type GP11 | 914226 GP11 |