

Garant GRIDLINE

**Large-capacity top-mounted cabinet with plain sheet metal swing doors,  
Height: 1000mm****Order data**

Order number	941011 1000
GTIN	4062406071462
Item class	9GI

**Description****Version:**

Equipped cabinet in 30×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Depth	700 mm
-------	--------

Number of shelves	1
Handle positioning	bottom
Height	1000 mm
Depth in G	28
Usable height	845 mm
Electronic locking system can be retrofitted	yes
Width	750 mm
ComfortClose	no
Width in G	30
Weight	70 kg
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Top-mounted cabinet
Type of product	Large-capacity cabinet

## Accessories

Inclined shelf foreForm for cabinet / compartment width in G 30	942550 30
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 75 mm	942570 75
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 300 mm	942570 300

Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm	940501 900/1000
Storage shelf with brackets 100 kg for cabinet / compartment width in G 30	942530 30
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 100 mm	942570 100
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm	942570 150
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 125 mm	942570 125
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 200 mm	942570 200
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 1000/1250 mm	940510 1000/1250
Slide handle for GridLine Type GP11	914226 GP11