

Garant GRIDLINE

Large-capacity base cabinet with Viewing window swing doors, Height: 1000mm**Order data**

| | |
|--------------|---------------|
| Order number | 941003 1000 |
| GTIN | 4062406071448 |
| Item class | 9GI |

Description**Version:**

Equipped cabinet in 30×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|---------------|--------|
| Usable height | 845 mm |
|---------------|--------|

| | |
|---|--|
| Width | 750 mm |
| ComfortClose | no |
| Handle positioning | top |
| Shelf load capacity / maximum distributed shelf load (on metal) | 100 kg |
| Depth in G | 28 |
| Electronic locking system can be retrofitted | yes |
| Depth | 700 mm |
| Number of shelves | 1 |
| Weight | 70 kg |
| Width in G | 30 |
| Height | 1000 mm |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1000 kg |
| Door opening angle | 250 degrees |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of cabinet | Base cabinet |
| Type of product | Large-capacity cabinet |

Accessories

| | |
|--|------------------|
| Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm | 940501 900/1000 |
| Inclined shelf foreForm for cabinet / compartment width in G 30 | 942550 30 |
| Push handle Type 1 | 958490 1 |
| | 940510 1000/1250 |

Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 1000/1250 mm

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 300 mm

942570 300

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 100 mm

942570 100

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 200 mm

942570 200

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm

942570 150

Slide handle for GridLine Type GP11

914226 GP11

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 125 mm

942570 125

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 75 mm

942570 75

Shelf clip set for GridLine cabinets 20 pieces Type F

940559 F

Storage shelf with brackets 100 kg for cabinet / compartment width in G 30

942530 30

Wheels and push handle retrofit set suitable for casing depth in G 28

958480 28