

Garant GRIDLINE

**Large-capacity base cabinet with Viewing window swing doors, Height: 1000mm****Order data**

Order number	941023 1000
GTIN	4062406071509
Item class	9GI

**Description****Version:**

Equipped cabinet in 40×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Electronic locking system can be retrofitted	yes
--	-----

Height	1000 mm
ComfortClose	no
Number of shelves	1
Handle positioning	top
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Width	1000 mm
Depth in G	28
Usable height	845 mm
Depth	700 mm
Width in G	40
Weight	81 kg
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Large-capacity cabinet

## Accessories

Push handle Type 1	958490 1
Inclined shelf foreForm for cabinet / compartment width in G 40	942550 40
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 100 mm	942573 100
	942573 75

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 75 mm

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 150 mm

942573 150

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 125 mm

942573 125

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 300 mm

942573 300

Wheels and push handle retrofit set suitable for casing depth in G 28

958480 28

Slide handle for GridLine Type GP11

914226 GP11

Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm

940501 900/1000

Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 1000/1250 mm

940511 1000/1250

Storage shelf with brackets 100 kg for cabinet / compartment width in G 40

942530 40

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm

942573 200

Shelf clip set for GridLine cabinets 20 pieces Type F

940559 F