

Garant GRIDLINE

Large-capacity base cabinet with plain sheet metal swing doors, Height: 2000mm**Order data**

Order number	941021 2000
GTIN	4062406071493
Item class	9GI

Description**Version:**

Equipped cabinet in 40×28G.

Mountings for shelves at 25mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	28
------------	----

Height	2000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Width in G	40
Number of shelves	4
Depth	700 mm
Width	1000 mm
Usable height	1845 mm
Electronic locking system can be retrofitted	yes
ComfortClose	no
Weight	146 kg
Handle positioning	centre
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Large-capacity cabinet

Accessories

Storage shelf with brackets100 kg for cabinet / compartment width in G 40	942530 40
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 200 mm	942573 200
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 150 mm	942573 150

Inclined shelf for cabinet / compartment width in G 40	942550 40
Basic lighting set for GridLine cabinets with swing doors for cabinet height 2000 mm	940501 2000
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 100 mm	942573 100
Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 2000 mm	940511 2000
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 75 mm	942573 75
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 125 mm	942573 125
Slide handle for GridLine Type GP11	914226 GP11
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 300 mm	942573 300
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F