

Garant GRIDLINE

Large-capacity base cabinet with Viewing window swing doors, Height: 2000mm



Order data

Order number	941023 2000
GTIN	4062406071516
Item class	9GI

Description

Version:

Equipped cabinet in 40×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
--	-----

Weight	146 kg
Height	2000 mm
Handle positioning	centre
Usable height	1845 mm
Width in G	40
Depth	700 mm
Number of shelves	4
Width	1000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
ComfortClose	no
Depth in G	28
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Large-capacity cabinet

Accessories

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 300 mm	942573 300
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 75 mm	942573 75
	942530 40

Storage shelf with brackets 100 kg for cabinet /
compartment width in G 40

Drawers for swing-door large-capacity cabinets and heavy-
duty cabinets Width 40G Drawer front height 200 mm

942573 200

Drawers for swing-door large-capacity cabinets and heavy-
duty cabinets Width 40G Drawer front height 150 mm

942573 150

Basic lighting set for GridLine cabinets with swing doors for
cabinet height 2000 mm

940501 2000

Drawers for swing-door large-capacity cabinets and heavy-
duty cabinets Width 40G Drawer front height 100 mm

942573 100

Inclined shelf for cabinet / compartment width in
G 40

942550 40

Drawers for swing-door large-capacity cabinets and heavy-
duty cabinets Width 40G Drawer front height 125 mm

942573 125

Extended lighting set for GridLine cabinets with swing
doors, width 40G for cabinet height 2000 mm

940511 2000

Slide handle for GridLine Type GP11

914226 GP11