

Garant GRIDLINE

Large-capacity base cabinet with Plain sheet metal sliding doors, Height: 2000mm**Order data**

Order number	941045 2000
GTIN	4062406071554
Item class	9GI

Description**Version:**

Equipped cabinet in 60×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
--	-----

Width	1500 mm
Height	2000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Handle positioning	centre
Depth	700 mm
Depth in G	28
Width in G	60
Number of shelves	8
Weight	239 kg
ComfortClose	no
Usable height	1863 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Large-capacity cabinet

Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm	942580 150
Lock plate for GridLine Type GP21	914227 GP21
Storage shelf with brackets 100 kg for cabinet / compartment width in G 30	942530 30
	942580 300

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 300 mm

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 75 mm

942580 75

Shelf clip set for GridLine cabinets
20 pieces Type F

940559 F

Inclined shelf foreForm for cabinet / compartment width in G 30

942550 30

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 125 mm

942580 125

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 200 mm

942580 200

Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 2000 mm

940514 2000

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 100 mm

942580 100