

Garant GRIDLINE

Large-capacity base cabinet with Plain sheet metal sliding doors, Height: 1000mm**Order data**

Order number	941045 1000
GTIN	4062406071547
Item class	9GI

Description**Version:**

Equipped cabinet in 60×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
Height	1000 mm
ComfortClose	no

Depth	700 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Weight	135 kg
Usable height	863 mm
Width in G	60
Number of shelves	2
Handle positioning	top
Depth in G	28
Width	1500 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Large-capacity cabinet

Accessories

Inclined shelf foreForm for cabinet / compartment width in G 30	942550 30
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 300 mm	942580 300
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 150 mm	942580 150
Lock plate for GridLine Type GP21	914227 GP21
	942530 30

Storage shelf with brackets 100 kg for cabinet /
compartment width in G 30

Drawers for sliding-door large-capacity cabinets and
heavy-duty cabinets Width 30G Drawer front height 200
mm

942580 200

Drawers for sliding-door large-capacity cabinets and
heavy-duty cabinets Width 30G Drawer front height 75 mm

942580 75

Drawers for sliding-door large-capacity cabinets and
heavy-duty cabinets Width 30G Drawer front height 100
mm

942580 100

Extended lighting set for GridLine cabinets with Sliding
doors, width 60G for cabinet height 1000/1250 mm

940514 1000/1250

Shelf clip set for GridLine cabinets 20 pieces Type F

940559 F

Drawers for sliding-door large-capacity cabinets and
heavy-duty cabinets Width 30G Drawer front height 125
mm

942580 125