

Garant GRIDLINE

**Large-capacity base cabinet with Plain sheet metal sliding doors, Height: 1000mm****Order data**

Order number	941065 1000
GTIN	4062406071608
Item class	9GI

**Description****Version:**

Equipped cabinet in 80×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Width	2000 mm
Height	1000 mm
ComfortClose	no
Depth	700 mm

Usable height	863 mm
Weight	160 kg
Width in G	80
Depth in G	28
Handle positioning	top
Number of shelves	2
Electronic locking system can be retrofitted	yes
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Large-capacity cabinet

## Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 125 mm	942583 125
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm	942583 200
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 300 mm	942583 300
Inclined shelf foreForm for cabinet / compartment width in G 40	942550 40
Lock plate for GridLine Type GP21	914227 GP21

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 75 mm	942583 75
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 100 mm	942583 100
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 150 mm	942583 150
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Storage shelf with brackets100 kg for cabinet / compartment width in G 40	942530 40
Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 1000/1250 mm	940515 1000/1250