

Garant GRIDLINE

Large-capacity base cabinet with Plain sheet metal sliding doors, Height: 2000mm**Order data**

Order number	941065 2000
GTIN	4062406071615
Item class	9GI

Description**Version:**

Equipped cabinet in 80×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	28
------------	----

Height	2000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Number of shelves	8
Width in G	80
Electronic locking system can be retrofitted	yes
Weight	266 kg
Depth	700 mm
Width	2000 mm
ComfortClose	no
Handle positioning	centre
Usable height	1863 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Large-capacity cabinet

Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 75 mm	942583 75
Inclined shelf foreForm for cabinet / compartment width in G 40	942550 40
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm	942583 200
	942530 40

Storage shelf with brackets 100 kg for cabinet /
compartment width in G 40

Lock plate for GridLine Type GP21

914227 GP21

Drawers for sliding-door large-capacity cabinets and
heavy-duty cabinets Width 40G Drawer front height 125
mm

942583 125

Drawers for sliding-door large-capacity cabinets and
heavy-duty cabinets Width 40G Drawer front height 150
mm

942583 150

Drawers for sliding-door large-capacity cabinets and
heavy-duty cabinets Width 40G Drawer front height 100
mm

942583 100

Extended lighting set for GridLine cabinets with Sliding
doors, width 80G for cabinet height 2000 mm

940515 2000

Shelf clip set for GridLine cabinets 20 pieces Type F

940559 F

Drawers for sliding-door large-capacity cabinets and
heavy-duty cabinets Width 40G Drawer front height 300
mm

942583 300