

Garant GRIDLINE

**Large-capacity base cabinet with Viewing window sliding doors, Height: 2000mm****Order data**

Order number	941067 2000
GTIN	4062406071639
Item class	9GI

**Description****Version:**

Equipped cabinet in 80×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Weight	266 kg
--------	--------

ComfortClose	no
Height	2000 mm
Depth	700 mm
Depth in G	28
Usable height	1863 mm
Number of shelves	8
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Width in G	80
Electronic locking system can be retrofitted	yes
Handle positioning	centre
Width	2000 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Large-capacity cabinet

## Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets  
Width 40G Drawer front height 100 mm

942583 100

Storage shelf with brackets  
100 kg for cabinet / compartment width in G 40

942530 40

Extended lighting set for GridLine cabinets with sliding doors, width 80G for cabinet height 2000 mm

940515 2000

942583 125

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets  
Width 40G Drawer front height 125 mm

Lock plate for GridLine Type GP21

914227 GP21

Inclined shelf foreForm for cabinet / compartment width in G 40

942550 40

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets  
Width 40G Drawer front height 150 mm

942583 150

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets  
Width 40G Drawer front height 300 mm

942583 300

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets  
Width 40G Drawer front height 200 mm

942583 200

Shelf clip set for GridLine cabinets  
20 pieces Type F

940559 F

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets  
Width 40G Drawer front height 75 mm

942583 75