

Garant GRIDLINE

Large-capacity top-mounted cabinet with Plain sheet metal sliding doors, Height: 1000mm



Order data

Order number	941075 1000
GTIN	4062406071646
Item class	9GI

Description

Version:

Equipped cabinet in 80×28G.

Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	28
Handle positioning	bottom
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg

Height	1000 mm
Width	2000 mm
Width in G	80
Number of shelves	2
Usable height	863 mm
Depth	700 mm
Weight	160 kg
Electronic locking system can be retrofitted	yes
ComfortClose	no
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Top-mounted cabinet
Type of product	Large-capacity cabinet

Accessories

Storage shelf with brackets 100 kg for cabinet / compartment width in G 40	942530 40
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm	942583 200
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 125 mm	942583 125
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 300 mm	942583 300

Inclined shelf for cabinet / compartment width in G 40	942550 40
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 100 mm	942583 100
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 150 mm	942583 150
Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 1000/1250 mm	940515 1000/1250
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 75 mm	942583 75
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Lock plate for GridLine Type GP21	914227 GP21