

Garant GRIDLINE

## Upright cabinet, depth 28G, 2 free-standing pull-out frames, Height: 1000 mm



### Order data

Order number	942002 1000
GTIN	4062406071660
Item class	9GI

### Description

#### Version:

Upright cabinet in 30×28G.

The upright cabinets are fitted **with free-standing pull-out frames. Each individual pull-out frame** is equipped with a lock so that only one pull-out frame can ever be open at a time. The pull-out frames have holes at intervals of 37 mm for mounting tool carriers, storage shelf trays and perforated tool boards. The upright cabinets are prepared for wall or floor–mounting and **must be secured against tilting**. The 2-component Haptoprene® push handle can be locked with a cylinder lock.

#### Optional extras:

The pull-out frames of the upright cabinets can be fitted with storage shelf trays No. 942010, perforated tool boards No. 942015, tool carriers No. 970130.

#### Colour:

Body RAL 7035 light grey, pull-out frames RAL 7016 anthracite **powder-coated**.

#### Note:

2 carriers can be fitted back-to-back in a 330-mm-wide pull-out frame.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Vertical pull-out frame load capacity: 350 kg

Height: 1000 mm

Width: 750 mm

Depth: 700 mm  
 Width in G: 30  
 Depth in G: 28  
 Pull-out frame drawers width: 330 mm

## Technical description

Width	750 mm
Vertical pull-out frame usable width	323 mm
Weight	181 kg
Vertical pull-out frame usable depth	627 mm
Pull-out frame drawers width	330 mm
Vertical pull-out frame load capacity	350 kg
Depth	700 mm
Vertical pull-out frame usable height	680 mm
Height	1000 mm
Width in G	30
Depth in G	28
Material thickness	1.2 mm
Cabinet housing internal load capacity	700 kg
Drawer runner extension	Anti-tilt lock
Height adjustment interval	37 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Upright cabinet