

Garant GRIDLINE

## Upright cabinet, depth 28G, 4 free-standing pull-out frames, Height: 2000 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 942004 2000   |
| GTIN         | 4062406071691 |
| Item class   | 9GI           |

### Description

#### Version:

Upright cabinet in 30×28G.

The upright cabinets are fitted **with free-standing pull-out frames. Each individual pull-out frame** is equipped with a lock so that only one pull-out frame can ever be open at a time. The pull-out frames have holes at intervals of 37 mm for mounting tool carriers, storage shelf trays and perforated tool boards. The upright cabinets are prepared for wall or floor–mounting and **must be secured against tilting**. The 2-component Haptoprene® push handle can be locked with a cylinder lock.

#### Optional extras:

The pull-out frames of the upright cabinets can be fitted with storage shelf trays No. 942010, perforated tool boards No. 942015, tool carriers No. 970130.

#### Colour:

Body RAL 7035 light grey, pull-out frames RAL 7016 anthracite **powder-coated**.

#### Note:

2 carriers can be fitted back-to-back in a 330-mm-wide pull-out frame.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Vertical pull-out frame load capacity: 175 kg

Height: 2000 mm

Width: 750 mm

Depth: 700 mm  
 Width in G: 30  
 Depth in G: 28  
 Pull-out frame drawers width: 160 mm

## Technical description

|  |  |
|--|--|
| Vertical pull-out frame usable depth   | 627 mm   |
| Width                                  | 750 mm   |
| Weight                                 | 252 kg   |
| Vertical pull-out frame usable width   | 153 mm   |
| Depth                                  | 700 mm   |
| Vertical pull-out frame load capacity  | 175 kg   |
| Pull-out frame drawers width           | 160 mm   |
| Height                                 | 2000 mm  |
| Vertical pull-out frame usable height  | 1680 mm  |
| Width in G                             | 30   |
| Depth in G                             | 28   |
| Material thickness                     | 1.2 mm   |
| Cabinet housing internal load capacity | 700 kg   |
| Drawer runner extension                | Anti-tilt lock   |
| Height adjustment interval             | 37 mm  |
| Cylinder lock                          | modular barrel   |
| Colour selection                       | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product                        | Upright cabinet  |