

Garant GRIDLINE

Heavy-duty cabinet with Viewing window swing door, Height: 1000mm**Order data**

Order number	942303 1000
GTIN	4062406071783
Item class	9GI

Description**Version:**

Equipped cabinet in 30x28G.

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	700 mm
Weight	76 kg

ComfortClose	no
Number of shelves	2
Depth in G	28
Height	1000 mm
Width in G	30
Usable height	845 mm
Electronic locking system can be retrofitted	yes
Handle positioning	top
Width	750 mm
Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

Accessories

Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm	940501 900/1000
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Push handle Type 1	958490 1
Wheels and push handle retrofit set suitable for casing depth in G 28	958480 28
Slide handle for GridLine Type GP11	914226 GP11
	940510 1000/1250

Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 1000/1250 mm

Heavy load shelf for cabinet / compartment width in G 30

942610 30