

Garant GRIDLINE

**Heavy-duty cabinet with Plain sheet metal swing door, Height: 1000mm****Order data**

Order number	942301 1000
GTIN	4062406071769
Item class	9GI

**Description****Version:**

Equipped cabinet in 30x28G.

**Reinforced side walls** to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Handle positioning	top
Weight	76 kg

Number of shelves	2
Height	1000 mm
Width	750 mm
Width in G	30
Usable height	845 mm
Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Depth in G	28
Electronic locking system can be retrofitted	yes
ComfortClose	no
Depth	700 mm
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

## Accessories

Wheels and push handle retrofit set suitable for casing depth in G 28	958480 28
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 1000/1250 mm	940510 1000/1250
Push handle Type 1	958490 1
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm	940501 900/1000

Heavy load shelf for cabinet / compartment width in G 30

942610 30