

**Adjustable spanner with coated handle, overall length: 200mm****Order data**

Order number	813961 200
GTIN	4062406069698
Item class	82A

**Description****Version:**

Slim design with double-T-profile shank. Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

With non-slip grip.

Adjustable spanner, chrome-plated.

**Technical description**

overall length	8 in
overall length	200 mm
maximum width across flats	24 mm
Jaw position	22 degrees
non-sparking	no
Scaling	yes
Grips	yes
Type of product	Adjustable spanners