

**Adjustable spanner with coated handle, overall length: 250mm****Order data**

Order number	813961 250
GTIN	4062406069704
Item class	82A

Description**Version:**

Slim design with double-T-profile shank. Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

With non-slip grip.

Adjustable spanner, chrome-plated.

Technical description

maximum width across flats	30 mm
overall length	10 in
overall length	250 mm
Jaw position	22 degrees
non-sparking	no
Scaling	yes
Grips	yes
Type of product	Adjustable spanners