

**Adjustable spanner with coated handle, overall length: 375mm****Order data**

Order number	813961 375
GTIN	4062406072025
Item class	82A

Description**Version:**

Slim design with double-T-profile shank. Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

With non-slip grip.

Adjustable spanner, chrome-plated.

Technical description

overall length	375 mm
overall length	15 in
maximum width across flats	44 mm
Jaw position	22 degrees
non-sparking	no
Scaling	yes
Grips	yes
Type of product	Adjustable spanners