



Adjustable spanner with coated handle, overall length: 300mm



Order data

Order number	813961 300
GTIN	4062406072018
Item class	82A

Description

Version:

Slim design with double-T-profile shank. Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

With non-slip grip.

Adjustable spanner, chrome-plated.

Technical description

overall length	12 in
overall length	300 mm
maximum width across flats	34 mm
Jaw position	22 degrees
non-sparking	no
Scaling	yes
Grips	yes
Type of product	Adjustable spanners