

**Adjustable spanner, overall length: 375mm****Order data**

Order number	814001 375
GTIN	4062406072094
Item class	82A

Description**Version:**

Slim design with double-T-profile shank. Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

Adjustable spanner, chrome-plated.

Technical description

maximum width across flats	44 mm
overall length	15 in
overall length	375 mm
Jaw position	22 degrees
Manufacturing process	drop-forged and hardened
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners