

Garant GRIDLINE

**Heavy-duty cabinet with Plain sheet metal sliding door, Height: 1000mm****Order data**

Order number	942345 1000
GTIN	4062406072520
Item class	9GI

**Description****Version:**

Equipped cabinet in 60×28G.

**Reinforced side walls** to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

ComfortClose	no
Electronic locking system can be retrofitted	yes
Number of shelves	4
Shelf load capacity / maximum distributed shelf load (on metal)	200 kg

Width in G	60
Depth in G	28
Height	1000 mm
Handle positioning	top
Width	1500 mm
Weight	88 kg
Depth	700 mm
Usable height	845 mm
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

## Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 100 mm	942580 100
Lock plate for GridLine Type GP21	914227 GP21
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 125 mm	942580 125
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 300 mm	942580 300
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm	942580 150
	942580 200

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets  
Width 30G Drawer front height 200 mm

Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 1000/1250 mm

940514 1000/1250

Shelf clip set for GridLine cabinets  
20 pieces Type F

940559 F

Heavy load shelf for cabinet / compartment width in G 30

942610 30

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets  
Width 30G Drawer front height 75 mm

942580 75