

Garant GRIDLINE

Heavy-duty cabinet with Viewing window sliding door, Height: 2000mm**Order data**

Order number	942347 2000
GTIN	4062406072551
Item class	9GI

Description**Version:**

Equipped cabinet in 60×28G.

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	2000 mm
Handle positioning	top

Depth	700 mm
Width in G	60
Number of shelves	10
Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Electronic locking system can be retrofitted	yes
Width	1500 mm
Usable height	1845 mm
Depth in G	28
ComfortClose	no
Weight	163 kg
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 300 mm	942580 300
Heavy load shelf for cabinet / compartment width in G 30	942610 30
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 125 mm	942580 125
Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 2000 mm	940514 2000
Lock plate for GridLine Type GP21	914227 GP21

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 150 mm

942580 150

Shelf clip set for GridLine cabinets20 pieces Type F

940559 F

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 75 mm

942580 75

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 100 mm

942580 100

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 200 mm

942580 200