

Garant GRIDLINE

Heavy-duty cabinet with Plain sheet metal sliding door, Height: 2000mm**Order data**

Order number	942345 2000
GTIN	4062406072537
Item class	9GI

Description**Version:**

Equipped cabinet in 60x28G.

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Handle positioning	top
ComfortClose	no

Number of shelves	10
Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Electronic locking system can be retrofitted	yes
Depth	700 mm
Height	2000 mm
Usable height	1845 mm
Width	1500 mm
Depth in G	28
Weight	163 kg
Width in G	60
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm	942580 150
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 75 mm	942580 75
Heavy load shelf for cabinet / compartment width in G 30	942610 30
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 125 mm	942580 125
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 100 mm

942580 100

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 200 mm

942580 200

Lock plate for GridLine Type GP21

914227 GP21

Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 2000 mm

940514 2000

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 300 mm

942580 300