

Garant GRIDLINE

## Heavy-duty cabinet with Plain sheet metal sliding door, Height: 1000mm



### Order data

Order number	942365 1000
GTIN	4062406072568
Item class	9GI

### Description

#### Version:

Equipped cabinet in 80x28G.

**Reinforced side walls** to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

#### Supplied with:

Cabinet with storage shelves.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Width in G	80
Electronic locking system can be retrofitted	yes
ComfortClose	no
Handle positioning	top
Height	1000 mm

Depth in G	28
Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Number of shelves	4
Width	2000 mm
Weight	173 kg
Depth	700 mm
Usable height	845 mm
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

## Accessories

Heavy load shelf for cabinet / compartment width in G 40	942610 40
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 125 mm	942583 125
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 100 mm	942583 100
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 75 mm	942583 75
Lock plate for GridLine Type GP21	914227 GP21
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 200 mm	942583 200
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 150 mm

942583 150

Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 1000/1250 mm

940515 1000/1250

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 300 mm

942583 300