

Garant GRIDLINE

Heavy-duty cabinet with Plain sheet metal sliding door, Height: 2000mm**Order data**

Order number	942365 2000
GTIN	4062406072575
Item class	9GI

Description**Version:**

Equipped cabinet in 80x28G.

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Depth in G	28

Usable height	1845 mm
Width in G	80
Depth	700 mm
Height	2000 mm
Electronic locking system can be retrofitted	yes
ComfortClose	no
Weight	312 kg
Handle positioning	top
Number of shelves	10
Width	2000 mm
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 100 mm	942583 100
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm	942583 200
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Lock plate for GridLine Type GP21	914227 GP21
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 125 mm	942583 125

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 150 mm	942583 150
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 75 mm	942583 75
Extended lighting set for GridLine cabinets withSliding doors, width 80G for cabinet height 2000 mm	940515 2000
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 300 mm	942583 300
Heavy load shelf for cabinet / compartment width in G 40	942610 40