

Garant GRIDLINE

Heavy-duty cabinet with Viewing window sliding door, Height: 1000mm



Order data

Order number	942347 1000
GTIN	4062406072544
Item class	9GI

Description

Version:

Equipped cabinet in 60×28G.

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabonets with reinforced cabinet base, without a levelling base.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Number of shelves	4
Depth	700 mm
ComfortClose	no

Handle positioning	top
Height	1000 mm
Weight	88 kg
Usable height	845 mm
Electronic locking system can be retrofitted	yes
Width in G	60
Depth in G	28
Width	1500 mm
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

Accessories

Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 1000/1250 mm	940514 1000/1250
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 300 mm	942580 300
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm	942580 150
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 200 mm	942580 200
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 75 mm	942580 75
	942580 100

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 100 mm

Heavy load shelf for cabinet / compartment width in G 30

942610 30

Shelf clip set for GridLine cabinets
20 pieces Type F

940559 F

Lock plate for GridLine Type GP21

914227 GP21

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 125 mm

942580 125