

Garant GRIDLINE

Heavy-duty cabinet with Viewing window sliding door, Height: 2000mm



Order data

Order number	942367 2000
GTIN	4062406072599
Item class	9GI

Description

Version:

Equipped cabinet in 80x28G.

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

ComfortClose	no
Handle positioning	top

Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Height	2000 mm
Depth in G	28
Usable height	1845 mm
Depth	700 mm
Electronic locking system can be retrofitted	yes
Width	2000 mm
Weight	312 kg
Number of shelves	10
Width in G	80
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

Accessories

Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Lock plate for GridLine Type GP21	914227 GP21
Heavy load shelf for cabinet / compartment width in G 40	942610 40
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 100 mm	942583 100
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 125 mm	942583 125
	942583 150

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 150 mm

Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 2000 mm

940515 2000

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm

942583 200

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 75 mm

942583 75

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 300 mm

942583 300